

DATENBLATT

DI-32B-PE

HABEN SIE FRAGEN ODER WÜNSCHEN SIE EIN INDIVIDUELLES ANGEBOT?

Unser Team berät Sie gerne persönlich.

TELEFON + 49 (0) 81 41/36 97-0

TELEFAX + 49 (0) 81 41/36 97-30

E-MAIL info@plug-in.de

WWW.PLUG-IN.DE

ADRESSE

Am Sonnenlicht 5

D-82239 Alling bei München



Opto-Isolation Digital Input for PCI Express
(On-board Power Supply)

DI-32B-PE



* Specifications, color and design of the products are subject to change without notice.

This product is a PCI Express bus-compliant interface board used to provide a digital signal I/O function on a PC. This product can input and output digital signals at 12 - 24VDC. DI-32B-PE features 32 opto-coupler isolated inputs. You can use 32 input signals as interrupt inputs. Equipped with the power for opto-coupler operation (12VDC) supplied and digital filter function to prevent wrong recognition of input signals. Windows/Linux driver is bundled with this product. Possible to be used as a data recording device for LabVIEW, with dedicated libraries.

Features

Opto-coupler isolated input (compatible with current sink output)

DI-32B-PE has the opto-coupler isolated input 32channels (compatible with current sink output) whose response speed is 200μsec. Common terminal provided per 16channels, capable of supporting a different external power supply. Supporting driver voltages of 12 - 24 VDC for I/O.

Opto-coupler bus isolation

As the PC is isolated from the input and output interfaces by opto-couplers, this product has excellent noise performance.

Power for opto-coupler operation (12VDC 240mA) supplied internally

As the power to run the opto-couplers is supplied internally, no external power supply is required. The use of jumpers allows you to decide whether you want to use the internal or external power supply for every 16 points.

You can use all of the input signals as interrupt request signals.

You can use all of the input signals as interrupt request signals and also disable or enable the interrupt in bit units and select the edge of the input signals, at which to generate an interrupt.

Windows/Linux compatible driver libraries are attached.

Using the attached driver library API-PAC(W32) makes it possible to create applications of Windows/Linux. In addition, a diagnostic program by which the operations of hardware can be checked is provided.

This product has a digital filter to prevent wrong recognition of input signals from carrying noise or a chattering.

This product has a digital filter to prevent wrong recognition of input signals from carrying noise or a chattering. All input terminals can be added a digital filter, and the setting can be performed by software.

Functions and connectors are compatible with PCI compatible board PI-32B(PCI)H.

The functions same with PCI compatible board PI-32B(PCI)H are provided. In addition, as there is compatibility in terms of connector shape and pin assignments, it is easy to migrate from the existing system.

LabVIEW is supported by a plug-in of dedicated library VI-DAQ.

Using the dedicated library VI-DAQ makes it possible to make a LabVIEW application.


Specification

Item	Specification
Input	
Input format	Opto-coupler isolated input (Compatible with current sink output) (Negative logic *1)
Number of input signal channels	32channels (all available for interrupts) (1 common in 16channels)
Input resistance	4.7kΩ
Input ON current	2.0mA or more
Input OFF current	0.16mA or less
Interrupt	32 interrupt input signals are arranged into a single output of interrupt signal INTA. An interrupt is generated at the rising edge (HIGH-to-LOW transition) or falling edge (LOW-to-HIGH transition).
Response time	Within 200μsec
Common	
Built-in power	12VDC 240mA *2
Allowable distance of signal extension	Approx. 50m (depending on wiring environment)
I/O address	Any 32-byte boundary
Interruption level	1 level use
Max. board count for connection	16 boards including the master board
Isolated Power	500Vrms
External circuit power supply	12 - 24VDC (±10%)
Power consumption (Max.)	When using the internal power supply : 3.3VDC 350mA, 12VDC 350mA When using the external power supply : 3.3VDC 350mA
Operating condition	0 - 50°C, 10 - 90%RH (No condensation)
Bus specification	PCI Express Base Specification Rev. 1.0a x1
Dimension (mm)	169.33(L) x 110.18(H)
Connector	37 pin D-SUB connector [F (female) type] DCLC-J37SAF-20L9E [mfd. by JAE] equivalent to it
Weight	140g
Certification	RoHS, CE, VCCI

*1 Data "0" and "1" correspond to the High and Low levels, respectively.

*2 When using the internal power supply, the input section consumes up to 40mA so the output current that can be supplied to the external device is 160mA.

Board Dimensions



The standard outside dimension (L) is the distance from the end of the board to the outer surface of the slot cover.

Support Software

Windows version of digital I/O driver API-DIO(WDM) / API-DIO(98/PC)

[Stored on the bundled Disk driver library API-PAC(W32)]
 The API-DIO(WDM) / API-DIO(98/PC) is the Windows version driver library software that provides products in the form of Win32 API functions (DLL). Various sample programs such as Visual Basic and Visual C++, etc and diagnostic program useful for checking operation is provided. You can download the updated version from the CONTEC's Web site (<http://www.contec.com/apipac/>). For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Linux version of digital I/O driver API-DIO(LNX)

[Stored on the bundled Disk driver library API-PAC(W32)]
 The API-DIO(LNX) is the Linux version driver software which provides device drivers (modules) by shared library and kernel version. Various sample programs of gcc are provided. You can download the updated version from the CONTEC's Web site (<http://www.contec.com/apipac/>). For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Data acquisition VI library for LabVIEW VI-DAQ (Available for downloading (free of charge) from the CONTEC web site.)

This is a VI library to use in National Instruments LabVIEW. VI-DAQ is created with a function form similar to that of LabVIEW's Data Acquisition VI, allowing you to use various devices without complicated settings. See <http://www.contec.com/vidaq/> for details and download of VI-DAQ.

Accessories

Accessories (Option)

- Screw Terminal (M3 x 37P) : EPD-37A *1*2
- Screw Terminal (M3.5 x 37P) : EPD-37 *1
- General Purpose Terminal : DTP-3A *1
- Screw Terminal : DTP-4A *1
- Signal Monitor for Digital I/O : CM-32(PC)E *1

*1 A PCB37P or PCB37PS optional cable is required separately.
 *2 "Spring-up" type terminal is used to prevent terminal screws from falling off.
 * Check the CONTEC's Web site for more information on these options.

Packing List

- Board [DI-32B-PE] ...1
- First step guide ... 1
- Disk *1 [API-PAC(W32)] ...1
- Serial number label...1
- Product Registration Card & Warranty Certificate...1

*1 The Disk contains the driver software and User's Guide.

Cable & Connector


Cable (Option)

- Flat Cable with Two 37-pin D- SUB Connectors
 - : PCB37P-1.5 (1.5m)
 - : PCB37P-3 (3m)
 - : PCB37P-5 (5m)
- Shielded Cable with Two 37-pin D- SUB Connectors
 - : PCB37PS-0.5P (0.5m)
 - : PCB37PS-1.5P (1.5m)
 - : PCB37PS-3P (3m)
 - : PCB37PS-5P (5m)
- Flat Cable with One 37-pin D- SUB Connector
 - : PCA37P-1.5 (1.5m)
 - : PCA37P-3 (3m)
 - : PCA37P-5 (5m)
- Shielded Cable with One 37-pin D- SUB Connector
 - : PCA37PS-0.5P (0.5m)
 - : PCA37PS-1.5P (1.5m)
 - : PCA37PS-3P (3m)
 - : PCA37PS-5P (5m)

Connector (Option)

- 37-pin D-SUB Male Connector Set (5 Pieces)
 - : CN5-D37M


Block Diagram



How to connect the connectors


Connector Shape

The on-board interface connector (CN1) is used when connecting this product and the external devices.



Connector Pin Assignment

< Pin Assignments of Interface Connector (CN1) >



I-00 - I-37 can be used as interrupt signal.


* The numbers in square brackets [] are pin numbers designated by HONDA TSUSHIN KOGYO CO., LTD.

I-00 - I-37	32 input signal pins. Connect output signals from the external device to these pins.
P0	When the external power supply is selected, its positive side is connected to these pins. When the internal power supply is used, these pins output power at +12 V. These pins are common to 16 input signal pins.
P1	When the external power supply is selected, its negative side is connected to this pin. When the internal power supply is selected, this pin serves as the ground. These pins are common to 16 input signal pins.
N0	When the external power supply is selected, its positive side is connected to these pins. When the internal power supply is used, these pins output power at +12 V. These pins are common to 16 input signal pins.
N1	When the external power supply is selected, its negative side is connected to this pin. When the internal power supply is selected, this pin serves as the ground. These pins are common to 16 input signal pins.
N.C.	This pin is left unconnected.

Connecting Input Signals

Connect the input signals to a device which can be current-driven, such as a switch or transistor output device. The board inputs the ON/OFF state of the current-driven device as a digital value.


- Input Circuit



The input circuits of interface blocks of the DI-32B-PE are illustrated above. Connect the input signals to a device which can be current-driven, such as a switch or transistor output device.

This product inputs the ON/OFF state of the current-driven device as a digital value. The signal inputs are isolated by opto-couplers (ready to accept current sinking output signals). This product therefore requires the on-board internal power supply or the external power supply to drive the input section of this product. In this case, 5.1mA current is requested each channel on 24VDC (2.6mA on 12VDC).

- Connecting a Switch



When the switch is ON, the corresponding bit contains 1.
When the switch is OFF, by contrast, the bit contains 0.

Connecting the Sink Type Output and Sink Output Support Input

The following example shows a connection between a sink type output (output board) and a sink output support input (input board). Refer to this connection example when you connect such boards to each other.

