

DATENBLATT

PIO-16/16L(LPCI)H

HABEN SIE FRAGEN ODER WÜNSCHEN SIE EIN INDIVIDUELLES ANGEBOT?

Unser Team berät Sie gerne persönlich.

TELEFON + 49 (0) 81 41/36 97-0

TELEFAX + 49 (0) 81 41/36 97-30

E-MAIL info@plug-in.de

WWW.PLUG-IN.DE

ADRESSE

Am Sonnenlicht 5

D-82239 Alling bei München



Digital I/O Board with Opto-Isolation for Low Profile PCI

PIO-16/16L(LPCI)H



* Specifications, color and design of the products are subject to change without notice.

Features

A different external power supply can be used for each common pin as it is shared by 16 channels.

The PCI bus (personal computer) and the I/O interface are isolated from each other by an opto-coupler, offering good noise immunity.

You can use all of the input signals as interrupt inputs. You can also select the interrupt trigger edge of the input signal.

The board has a digital filter feature to prevent noise or chatter from causing erroneous inputs.

Up to 35VDC, 100mA per signal, max. output.

Zener diode connected to output transistors for protection from surge voltage. Overcurrent protective device provided for every eight channels of output transistors.

Support for both of low-profile and standard PCI slots (interchangeable with a bundled bracket).

This board is a PCI-compliant interface board for input/output of digital signals. The board can input and output digital signals at 12 - 24 VDC. The board supports a low-profile PCI slot and, if replaced with the supplied bracket, supports a PCI slot, too. PIO-16/16L(LPCI)H can input and output up to 16 channels. Using the bundled API function library package [API-PAC(W32)], you can create Windows application software for this board in your favorite programming language supporting Win32 API functions, such as Visual Basic or Visual C/C++.


Specification

Item	Specification
Input	
Input format	Opto-isolated input (Compatible with current sink output)(Negative logic *1)
Number of input signal channels	16 channels (all available for interrupts) (1 common)
Input resistance	4.7kΩ
Input ON current	2.0mA or more
Input OFF current	0.16mA or less
Interrupt	16 interrupt input signals are arranged into a single output of interrupt signal INTA. An interrupt is generated at the rising edge (HIGH-to-LOW transition) or falling edge (LOW-to-HIGH transition).
Response time	200μsec within
Output	
Output format	Opto-isolated open collector output (current sink type) (Negative logic*1)
Number of output signal channels	16 channels (1 common)
Output rating	35VDC (Max.)
Output voltage	100mA (par channel) (Max.)
Output current	
Residual voltage with output on	0.5V or less (Output current≤50mA), 1.0V or less (Output current≤100mA)
Surge protector	Zener diode RD47FM(NEC) or equivalent
Response time	200μsec within
Common	
I/O address	Any 32-byte boundary
Interruption level	1 level use
Max. board count for connection	16 boards including the master board
Dielectric strength	1000Vrms
External circuit power supply	12 - 24VDC(±10%)
Power consumption	5VDC 100mA(Max.)
Operating condition	0 - 50°C, 10 - 90%RH (No condensation)
Allowable distance of signal extension	Approx. 50m (depending on wiring environment)
PCI bus specification	33bit, 33MHz, Universal key shapes supported *2
Dimension (mm)	121.69(L) x 63.41(H)
Weight	60g
Certification	RoHS,CE,VCCI

*1 Data "0" and "1" correspond to the High and Low levels, respectively.

*2 This board requires power supply at +5 V from an expansion slot (it does not work on a machine with a +3.3-V power supply alone).

Board Dimensions



The standard outside dimension (L) is the distance from the end of the board to the outer surface of the slot cover.

Support Software

Driver Software Package API-PAC(W32) (Available for downloading (free of charge) from the CONTEC web site.)

API-PAC(W32) is the library software that provides the commands for CONTEC hardware products in the form of Windows standard Win32 API functions (DLL). It makes it easy to create high-speed application software taking advantage of the CONTEC hardware using various programming languages that support Win32 API functions, such as Visual Basic and Visual C/C++.

It can also be used by the installed diagnosis program to check hardware operations.

CONTEC provides download services to supply the updated drivers and differential files.

For details, read Help on the bundled Disk visit the CONTEC's Web site.

Linux version of digital I/O driver API-DIO(LNX) (Supplied: Stored on the API-PAC(W32) Disk)

This driver is used to control CONTEC digital I/O boards (cards) from within Linux.

You can control CONTEC I/O boards easily using the shared library used by gcc and Kylix, the device driver (module) for each kernel version, and the board (card) configuration program (config).

CONTEC provides download services to supply the updated drivers and differential files.

For details, read Help on the bundled Disk or visit the CONTEC's Web site.

Data acquisition VI library for LabVIEW VI-DAQ (Free download)

This is a VI library to use in National Instruments LabVIEW. VI-DAQ is created with a function form similar to that of LabVIEW's Data Acquisition VI, allowing you to use various devices without complicated settings.

See <http://www.contec.com/vidaq/> for details and download of VI-DAQ.

Cable & Connector

Cable(Optional)

Shield Cable with Two 50-Pin Mini-Ribbon Connector

- : PCB50PS-0.5P(0.5m)
- : PCB50PS-1.5P(1.5m)
- : PCB50PS-3P(3m)
- : PCB50PS-5P(5m)

Shield Cable with One 50-Pin Mini-Ribbon Connector

- : PCA50PS-0.5P(0.5m)
- : PCA50PS-1.5P(1.5m)
- : PCA50PS-3P(3m)
- : PCA50PS-5P(5m)

Connection Conversion 0.5m Shield Cable (50-Pin Ribbon->37-Pin D-SUB) : PCE50/37PS-0.5P(0.5m)

Packing List

Board [PIO-16/16L(LPCI)H] ...1
 First step guide ... 1
 Disk *1 [API-PAC(W32)] ...1
 Bracket for PCI...1
 Serial number label...1
 Product Registration Card & Warranty Certificate...1

*1 The Disk contains the driver software and User's Guide.

Accessories

Accessories (Option)

Screw Terminal Unit(M3 terminal block, 50 points)
 : EPD-50A *1

Screw Terminal Unit(M3 terminal block, 37 points)
 : EPD-37A *2

Screw Terminal Unit(M3.5 terminal block, 37 points)
 : EPD-37 *2

Termination Panel (M3)
 : DTP-3(PC) *3

Termination Panel
 : DTP-4(PC) *3

Signal Monitor for Digital I/O
 : CM-32(PC)E *2


*1 PCB50PS-*P optional cable is required separately.
 *2 PCE50/37PS-0.5P and PCB37P or PCB37PS optional cable is required separately.
 *3 PCE50/37PS-0.5P optional cable is required separately.

* Check the CONTEC's Web site for more information on these options.

How to connect the connectors

Connecting a Device to a Connector

To connect an external device to this board, plug the cable from the device into the interface connector shown below.




Connector Pin Assignment

Common minus pin for +2/+3 output ports	ON 2/3	50	50	25	ON 2/3	25	Common minus pin for +2/+3 output ports
	ON 2/3	49			24	ON 2/3	
	O-20	48			23	O-30	
	O-21	47			22	O-31	
	O-22	46			21	O-32	
	O-23	45			20	O-33	
	O-24	44			19	O-34	
+2 port (output)	O-25	43	26	1	18	O-35	+3 port (output)
	O-26	42			17	O-36	
	O-27	41			16	O-37	
	OP 2/3	40			15	OP 2/3	
	OP 2/3	39			14	OP 2/3	
	N.C.	38			13	N.C.	
	N.C.	37			12	N.C.	
+0 port (input)	N.C.	36	26	1	11	N.C.	+1 port (input)
	I-00	35			10	I-10	
	I-01	34			9	I-11	
	I-02	33			8	I-12	
	I-03	32			7	I-13	
	I-04	31			6	I-14	
	I-05	30			5	I-15	
Common plus pin for +0/+1 input ports	I-06	29	26	1	4	I-16	Common plus pin for +0/+1 input ports
	I-07	28			3	I-17	
	IP 0/1	27			2	IP 0/1	
IP 0/1	27	1	IP 0/1	1	IP 0/1		


I-00 - I-17	16 input signal pins. Connect output signals from the external device to these pins.
O20 - O37	16 output signal pins. Connect these pins to the input signal pins of the external device.
IP 0/1	Connect the positive side of the external power supply. These pins are common to 16 input signal pins.
OP 2/3	Connect the positive side of the external power supply. These pins are common to 16 output signal pins.
ON 2/3	Connect the negative side of the external power supply. These pins are common to 16 output signal pins.
N.C.	This pin is left unconnected.

Example of Connection to TTL Level Input




Connecting the Sink Type Output and Sink Output Support Input

The following example shows a connection between a sink type output (output board) and a sink output support input (input board). Refer to this connection example when you connect such boards to each other.



Block Diagram



Differences between the PIO-16/16L(LPCI)H and PIO-16/16L(PCI)H

The PIO-16/16L(LPCI)H is connector-pin compatible with the conventional PIO-16/16L(PCI)H but has the following differences from it:

- (1) Different in connector shape and pin assignment
 PIO-16/16L(LPCI)H : 50-Pin Mini-Ribbon connector
 PIO-16/16L(PCI)H : 37-Pin D-SUB
- (2) Different in board dimensions
 PIO-16/16L(LPCI)H : 121.69(L) x 63.41(H) mm
 PIO-16/16L(PCI)H : 121.69(L) x 105.68(H) mm